

COLUMNAS


Columna Guía GC

Material: 1,7264

Tratamiento: Carbonitrurado prof. 0,6

Dureza: 60-62 HRC

Forma de pedido: GC/d₁ x l₁ x L



d ₁	d ₂	D	a	b	L ₁	L														
						18	26	36	45	50	65	70	90	100	125	150	175	200		
10	14	17	4	4	17			•												
					50	•	•													
					70	•														
					80	•														
12	16	20	4	4	17	•	•	•	•		•									
					26		•	•	•		•		•							
					34		•	•	•		•		•							
					44		•	•	•		•		•							
					54		•	•	•		•		•							
16	20	24	4	4	20	•	•	•	•		•		•		•					
					26		•	•	•		•		•		•		•			
					34		•	•	•		•		•		•		•		•	
					44		•	•	•		•		•		•		•		•	
					54		•	•		•		•		•		•		•		•
					74			•		•		•		•		•		•		•
18	25	30	6	6	20		•	•	•		•		•		•		•			
					26		•	•	•		•		•		•		•		•	
					34			•	•		•		•		•		•		•	
					44			•	•		•		•		•		•		•	
					54			•		•		•		•		•		•		•
					74			•		•		•		•		•		•		•
22	30	35	6	6	26			•	•		•		•		•		•			
					34			•	•		•		•		•		•		•	
					44			•	•		•		•		•		•		•	
					54			•		•		•		•		•		•		•
					64			•		•		•		•		•		•		•
					74			•		•		•		•		•		•		•
25	35	40	8	6	26			•	•		•		•		•		•			
					34			•	•		•		•		•		•		•	
					44				•		•		•		•		•		•	
					54			•		•		•		•		•		•		•
					64			•		•		•		•		•		•		•
					74			•		•		•		•		•		•		•
30	40	45	8	7	26			•	•		•		•		•		•			
					34			•	•		•		•		•		•		•	
					44				•		•		•		•		•		•	
					54			•		•		•		•		•		•		•
					74			•		•		•		•		•		•		•
					94			•		•		•		•		•		•		•
40	50	54	10	8	70								•			•				