


# COLUMNAS

## Columna Guía GC2


Material: 1,7264  
 Tratamiento: Carbonitrurado prof. 0,6  
 Dureza: 60-62 HRC  
 Forma de pedido: GC2/di x li x L



d <sub>1</sub>	d <sub>2</sub>	D	a	b	s	L <sub>1</sub>	L										
							26	36	45	50	65	70	100				
12	16	20	4	4	12	26	•		•								
						17	•		•								
16	20	24	4	4	12	26					•						
						34		•									
						44		•									
						54		•									
18	25	30	6	6	14	34			•				•				
						44			•					•			
22	30	35	6	6	14	44					•			•		•	•
						54					•			•		•	•
						64					•			•		•	•

## Columna Guía G

Material: 1,7264  
 Tratamiento: Carbonitrurado prof. 0,6  
 Dureza: 60-62 HRC  
 Forma de pedido: G/di x li x L



d <sub>1</sub>	D	a	b	L															
				44	52	65	75	85	95	105	115	125	140	170	200	220	250	280	315
10	12	4	3	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
12	15	4	4	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
14	17	5	4	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
16	19	6	5	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
18	22	6	6			•	•	•	•	•	•	•	•	•	•	•	•	•	•
20	24	7	6			•	•	•	•	•	•	•	•	•	•	•	•	•	•
25	30	8	7				•	•	•	•	•	•	•	•	•	•	•	•	•
30	35	10	8					•	•	•	•	•	•	•	•	•	•	•	•